

Why NK loupe?

German mineral lens

P Premium lens

Building User Convenience

- NK's frame design is lighter than flip-up type and other company's TTL loupes by ergonomically designing. and this stable frame is made of pure titanium and is coted with special plating, and cut off the source of allergy.
- 2. It has a wide field and depth by using mineral lenses.

Correct posture

NK Loupes help you correct your posture by guiding you to the right posture.

It provides a large view of the image to reduce eye strain. It's easier and more precise to practice.









Adventage of TTL loupe

- 1. TTL loupes are attached to glasses, so it has a wide visibility because they are close to the distance.
- 2. TTL loupes are light because they don't have PD control device.

Magnification Option (ex. Working Distance : 40cm)















SILVER



BLACK

NK00 SIZE 144_50_144

Style	TTL
Magnification	x2.5 / x3.0 / x3.3 / x3.8 / x5.0 / x6.0
Model name	NK 00
Color	Blue / Wine / Silver / Black






NK01 SIZE 142_48_144

Style	TTL
Magnification	x2.5 / x3.0 / x3.3 / x3.8 / x5.0 / x6.0
Model name	NK 01
Color	lvory_Black / Red_Black / Green_Brown / Black



Flip-up x2.5 / x3.0

Style	Flip- up
Magnification	x2.5 / x3.0
Model name	NK-F
Color	Black, Blue, Red, Silver




Goggle x2.5 / x3.0

Style	Goggle
Magnification	x2.5 / x3.0
Model name	NK-G
Color	Black, Gray, Blue, Green, Red, Orange



LED Light Wire & Wireless


Style	LED Light	
Brightness	55,000 Lux ~ 140,000 Lux	
Model name	NK Multi Light	
Light Color	White + Yellow	



Battery Light battery

Style	Battery	Wireless Battery
Bufferung hour	7~10 hr	60min ~ 100min
Charging times allowed	600 times	300 times
Color	Black	Black

Detail





Office: 227, Gonghang-daero, Gangseo-gu, Seoul, Republic of Korea Factory: 59, Hakjeongdong-ro, Buk-gu, Daegu, Republic of Korea

TEL.+82 - 70-4134-7257 Email. nkvision1001@gmail.com



www.nkvision.net